

TECHNICAL SPECIFICATIONS				
Picture				
Model	YF-01	YN-02	YF-03	YN-01
Type	Full Face Mask	Nasal Mask	Full Face Mask	Nasal Mask
Therapy Pressure Range	4-30 cmH ₂ O	4-30 cmH ₂ O	4-30 cmH ₂ O	4-30 cmH ₂ O
Tube Connection	φ22mm	φ22mm	φ22mm	φ22mm
Flow Resistance(At 50 L/min)	≤0.5cmH ₂ O	≤0.5cmH ₂ O	≤0.5cmH ₂ O	≤0.5cmH ₂ O
Flow Resistance(At 100 L/min)	≤1.5cmH ₂ O	≤1.5cmH ₂ O	≤1.5cmH ₂ O	≤1.5cmH ₂ O
Expiratory Resistance with Anti Asphyxia Valve Open (At 50 L/min)	≤2.0cmH ₂ O/(L/S)	—	≤2.0cmH ₂ O/(L/S)	—
Inspiratory Resistance with Anti Asphyxia Valve Open (At 50 L/min)	≤2.0cmH ₂ O/(L/S)	—	≤2.0cmH ₂ O/(L/S)	—
Anti Asphyxia Valve Open Pressure	≤2.0cmH ₂ O/(L/S)	—	≤2.0cmH ₂ O/(L/S)	—
Anti Asphyxia Valve Closed Pressure	≤2.0cmH ₂ O/(L/S)	—	≤2.0cmH ₂ O/(L/S)	—
G.W./N.W.	147/106g	90/60g	139/103g	101/63g
Packing	10PCS/CTN 35×28×28cm	10PCS/CTN 35×24×24cm	10PCS/CTN 35×28×28cm	10PCS/CTN 35×24×24cm

TECHNICAL SPECIFICATIONS			
Picture			
Model	YF-02	YN-03	YP-01
Type	Full Face Mask	Nasal Mask	Pillow Mask
Therapy Pressure Range	4-30 cmH ₂ O	4-30 cmH ₂ O	4-20 cmH ₂ O
Tube Connection	φ22mm	φ22mm	φ22mm
Flow Resistance(At 50 L/min)	≤0.5cmH ₂ O	≤0.5cmH ₂ O	≤0.5cmH ₂ O
Flow Resistance(At 100 L/min)	≤1.5cmH ₂ O	≤1.5cmH ₂ O	≤1.5cmH ₂ O
Expiratory Resistance with Anti Asphyxia Valve Open (At 50 L/min)	≤2.0cmH ₂ O/(L/S)	—	—
Inspiratory Resistance with Anti Asphyxia Valve Open (At 50 L/min)	≤2.0cmH ₂ O/(L/S)	—	—
Anti Asphyxia Valve Open Pressure	≤2.0cmH ₂ O/(L/S)	—	—
Anti Asphyxia Valve Closed Pressure	≤2.0cmH ₂ O/(L/S)	—	—
G.W./N.W.	148/107g	129/99g	268/81g
Packing	10PCS/CTN 35×28×28cm	10PCS/CTN 35×28×28cm	10PCS/CTN 34×22×24.5cm